



Model(s) Z826B2-XL

AquaSpec® lab faucet with 5-3/8" gooseneck and cross handles

TAG _____

Architectural/Engineering Specification:

Polished chrome-plated double laboratory faucet with integral shank, quarter turn ceramic disc cartridges and a 5-3/8" [137mm] centerline rigid or swing gooseneck spout. Unit is furnished with a 2.2 GPM [8.3 L] pressure compensating aerator (complying with ANSI A112.18.1 Standard for flow), vandal-resistant color-coded metal four arm handles, mounting hardware and stainless steel flex connection hoses.

Zurn Lead Free products (-XL) is the line of durable, high quality brass faucets and fixtures that are designed and manufactured to comply with Section 1417 of the Safe Drinking Water Act (SDWA) which mandates the weighted average lead content of no more than 0.25% of the wetted surface.

PRODUCT FEATURES:

- Heavy-duty Quarter Turn Ceramic Disc Cartridge
- Chrome-plated Cast Brass Body with Integral Shank
- Stainless Steel Flex Connection Hoses
- Vandal resistant color coded 4 arm handles
- Chrome-plated Cast Brass Body With Integral Shank

SUFFIX OPTIONS:

| | | |
|--------------------------|-----|---|
| <input type="checkbox"/> | -AR | Anti-Rotation Pins |
| <input type="checkbox"/> | -CS | Check Stops |
| <input type="checkbox"/> | -G | 1-1/4" [32mm] Grid Strainer Drain |
| <input type="checkbox"/> | -MY | Mixing Yoke Assembly Instead of Braided Hoses |

AERATOR OPTIONS:

| | Suffix | Flowrate GPM [L] | Vandal- Resistant | Pressure Compensating | Outlet Type |
|--------------------------|--------|---------------------|----------------------|--------------------------|-------------|
| <input type="checkbox"/> | -16F | 1.0 GPM [3.8L] | x | x | Spray |
| <input type="checkbox"/> | -17F | 1.5 GPM [5.7L] | x | x | Aerator |
| <input type="checkbox"/> | -18F | 1.5 GPM [5.7L] | x | x | Laminar |
| <input type="checkbox"/> | -22F | 1.0 GPM [3.8L] | x | | Laminar |
| <input type="checkbox"/> | -25F | 0.35 GPM [1.3L] | x | x | Spray |
| <input type="checkbox"/> | -27F | 0.5 GPM [1.9L] | | | Laminar |
| <input type="checkbox"/> | -28F | 0.5 GPM [1.9L] | x | | Laminar |
| <input type="checkbox"/> | -2F | 2.2 GPM [8.3L] | x | | Aerator |
| <input type="checkbox"/> | -3F | 0.5 GPM [1.9L] | x | | Spray |
| <input type="checkbox"/> | -4F | 2.2 GPM [8.3L] | x | | Laminar |
| <input type="checkbox"/> | -7F | 1.0 GPM [3.8L] | | x | Spray |
| <input type="checkbox"/> | -FC0.5 | 0.5 GPM [1.9L] | | x | |
| <input type="checkbox"/> | -FC1.0 | 1.0 GPM [3.8L] | | x | |
| <input type="checkbox"/> | -FC1.5 | 1.5 GPM [5.7L] | | x | |
| <input type="checkbox"/> | -FC2.0 | 2.0 GPM [7.6L] | | x | |



Product Compliance:

ASME A112.18.1/CSA B125.1
CSA B125.1


**Although products with certain combinations of options and features will meet or comply with these standards and/or certifications, not every combination of options and features will result in such compliance. If you have any questions about your particular product, please contact our Customer Care Dept. at 1-855-ONE-ZURN (United States) or 1-877-892-5216 (Canada) for confirmation.*

[Installation Guide - CF1552.pdf](#)

Architectural/Engineering Approval

Design and dimensional data (inches and [mm]) are subject to manufacturing tolerances and change without notice.

⚠ WARNING: Cancer and Reproductive Harm – www.P65warnings.ca.gov
⚠ ADVERTENCIA: Cáncer y daño reproductivo – www.P65warnings.ca.gov
⚠ AVERTISSEMENT: Cancer et effets néfastes sur la reproduction – www.P65warnings.ca.gov



NOTE: All dimensions are for reference only. Do not use for pre-plumbing.

Design and dimensional data (inches and [mm]) are subject to manufacturing tolerances and change without notice.

⚠ WARNING: Cancer and Reproductive Harm – www.P65warnings.ca.gov
 ⚠ ADVERTENCIA: Cáncer y daño reproductivo – www.P65warnings.ca.gov
 ⚠ AVERTISSEMENT: Cancer et effets néfastes sur la reproduction – www.P65warnings.ca.gov